

## WatcoFlex®

## **SPECIFICATIONS**

#### WatcoFlex® Features and Benefits:

- Eliminates four Schedule 40 solvent-weld field joints. resulting in significant installed-cost savings.
- Designed with a direct drain layout, which can be easier and faster to install.
- All joints are factory sealed and tested; no solvent weld.
- Eliminates the scrap that results from cutting and fitting and the need to provide extra pipe or sanitary tee.

#### Innovator® Features and Benefits:

- · No screws to handle, install, or lose.
- No damage from errant screwdrivers.
- No need to caulk overflow gasket, which is flexible to compensate for the slope and curvature of different tubs.
- · No callbacks; eliminates alignment problems and leaks.

## **Approvals:**

- · Non-corrugated, flexible PVC tubing.
- Manufactured in compliance with ASME A112.18.2-2005/ CSA B125.2-05; and IAPMO PS 69-2006.

## Patents (Innovator®):

- U.S. Pat. Numbers 5,890,241; 6,637,050; 6,675,406; 7,127,752; and Patents Pending
- Canadian Patent Number 2,437,448
- Mexican Patent Numbers PA/a/2003007344; PA/a/2005002784; PA/a/2005011301

## Patents (WatcoFlex®):

- U.S. Patent Pending
- Mexican Patent Number PA/a/2005011301

#### **Thread Size:**

- 11/2" 111/2 NPSM (Coarse Thread)
- 1.865" Major Diameter (outside thread diameter)
- 11.5 threads per inch

☐ ABS Piping: Schedule 40: ☐ PVC









Includes built-in Easily remove test membrane membrane after test overflow plate.

Snap-on No screws

## NOTE:

CONTACT WATCO WITH NAME OF MANUFACTURER AND TUB MODEL NUMBER SO CORRECT LENGTH OF FLEX TUBING CAN BE OBTAINED.

## 통 ADA

PRESFLO® (PF) and Foot Actuated (FA) only

See price list for complete item number and available options.

When ordering, please specify complete catalog number and option codes.


## For more information, contact:

# WATCO


**WATCO Manufacturing Company** 1220 South Powell Road

Independence, MO 64057-2724 Ph. 816-796-3900 • 800-821-8576 Fax 816-796-0875 • 800-399-2826 www.watcomfg.com

## ROUGH-IN (RI's) and STOPPER/FACEPLATE (SF's)



## WatcoFlex® Series




Item	Part # C	Description			
1.	01010CPK	nob, Brass			
2.	11510F	riction Ring and Post (11505 & 11532)			
3.	01013CPS	topper, Brass			
4.	11507S	eal, 1 <sup>1</sup> / <sub>16</sub> " dia.			
5.	01016CPS	trainer Body, 1.865" - 11.5			
6.	10696D	rain Ell Washer, 1.5" gray			
7.		ubing Factory-Assembled with:			
1		Firect Drain Tee, Schedule 40 ABS			
1		nnovator® Overflow Ell, Sch. 40 ABS			
1		nnovator® Membrane, ABS/PVC blend			
1	<u>OR</u>	tine at Duain Too. Cabadula 40 DVC			
1		virect Drain Tee, Schedule 40 PVC nnovator® Overflow Ell, Sch. 40 PVC			
1		nnovator® Membrane, ABS/PVC blend			
8.		Overflow Ell Washer, Foam			
9.		Retainer Nut for Innovator®			
10.		Overflow Plate for Innovator®			
11.		est Plug with "O"-Ring-type Gasket			
		3 3 4 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5 5			
* SE: (example: 900-PPSE) Parts #1 thru #4 and #10					

\* SF: (example: 900-PP<u>SF</u>) Parts #1 thru #4, and #10

\*\* RI: (example: FLEX145-PPRI) Parts #5 thru #9, and #11

## OPTIONAL TUB CLOSURES FOR FLEX BATH WASTES (PUSH PULL® ALSO SHOWN ABOVE)



## WHEN ORDERING, PLEASE PROVIDE THE TUB MANUFACTURER AND MODEL NUMBER.

NOTE: The length portion of the product number will be determined by the tub's dimensions.

## Examples:

FLEX<u>145</u> will have 14.5" of flexible tubing; FLEX<u>170</u> will have 17.0" of flexible tubing.

NOTE: This product should not need to be stretched or compressed to fit the tub.

If it does not fit easily, call the factory to get the correct size for that tub.

## Finishes Available in the WatcoFlex Series:

Tub Closures:	PUSH PULL®	LIFT & TURN	PRESFLO®	FOOT ACT.
CP - Chrome Plated	•	•	•	•
AB - Antique Brass				
AP - Aged Pewter	•	•	•	
BB - Brushed Bronze	•	•	•	
BN - Brushed Nickel	•	•	•	•
BO - Bone	•	•		
BS - Biscuit	•	•		
BZ - Oil-Rubbed Bronze	•	•	•	•
CB - Chrome Brushed	•	•	•	
NP - Nickel Polished	•	•	•	•
PB - Polished Brass	•	•	•	•
PN - Pearl Nickel	•	•	•	
WH - White	•	•		
WI - Wrought Iron	•	•	•	